

### AP26BCF-3T Modular Blast Chiller

PROJECT NAME:	_
ITEM #:	_
OTV RECILIBED.	

## **SPECIFICATIONS**

**GENERAL:** This specification covers the model AP26BCF-3T which is sized for three mobile racks (not included) with maximum dimensions of  $26\text{"W} \times 36\text{"D} \times 73.5\text{"H}$ . See chart on reverse side for production capacity. One core temperature probe is provided for accurate control of temperature within the product.

**PERFORMANCE:** Blast chilling (soft or hard) lowers the food core temperature from 160°F to 38°F within 90 minutes. Chilling times will vary somewhat, depending on the food quantity, initial temperature, density, moisture content, specific heat, and type of container. The airflow has a high velocity, indirect pattern designed to cool all levels at identical rates. Time/temperature chilling rates meet or exceed all FDA, NSF, and state regulations.

**CONSTRUCTION:** The chilling cabinet is constructed of polished type 304 stainless steel, with 4" of CFC-free, high density polyurethane insulation. The interior corners are fully rounded. The door is equipped with a removable magnetic gasket. All motors are sealed ball bearing wash-down type. A minimum 15" clear space required above the cabinet for service. Provide 12" clearance on the hinge side of the cabinet to allow for door opening.

**ASSEMBLY:** Unit manufactured using insulated panels and camlock style assembly allowing for easy ingress through standard building door openings.

**REFRIGERATION SYSTEM:** The cabinet refrigeration system is complete with all components, including controls, evaporator coil and blower system. The evaporator is of the forced convection type and designed specifically for blast chilling operation. Air circulation motors, multi-fin and tube type coils, and fan guards are contained within the cabinet. Access to the evaporator for cleaning shall be via a convenient hinged, swing-out ventilator panel. Fan motors have inherent overload protection and the fan blades are guarded to prevent injury.

**TOUCH SCREEN CONTROL SYSTEM:** The control system features a 7" glove-safe capacitive touchscreen that can be easily observed from across the kitchen. The user friendly interface allows easy and quick access to all the chilling or freezing cycles, auxiliary cycles, and settings. A Quick Start button offers the convenience of starting any chilling or freezing cycle with one touch.



**Soft Chilling:** The air temperature is held in the range of 28°F to 35°F, ideal for delicate food items. The chilling cycle is completed when the food core temperature reaches 38°F to 40°F.

**Hard Chilling:** The air temperature is lowered to and held within a range of 10°F to 20°F. When the food core temperature reaches 60°F, the air temperature rises to a range of 28°F to 35°F. The chilling cycle is completed when the food core temperature reaches 38°F to 40°F.

**Shock Freezing:** This cycle is designed to avoid damage to the food structure, keeping the food free of large ice crystals. The air temperature is lowered to and held at -25°F. The freezing cycle is completed when the food core temperature reaches 0°F.


**Holding:** At the end of any cycle, the unit will automatically switch to a holding mode which will keep the food at holding temperature until the cycle is stopped.

# **ADDITIONAL FEATURES:**

**Defrost:** An automatic defrost cycle is factory preset to initiate during the early morning but can be customized. A manual defrost cycle can run on demand as needed.

**Product Names:** Store up to 150 product names that can be used to help identify cycle runs within the HACCP reports.





CABINET DATA		CA	SHIPPING			
MODEL	V	HZ	РН	Α	REQUIRED CIRCUIT [A]	WEIGHT [LBS]
AP26BCF-3T	208	60	1	22.7	30.0	3,349

CYCLE TIME	160°F - 38°F	160°F - 0°F
90 Minutes	780 lbs.	
120 Minutes	900 lbs.	
240 Minutes		468 lbs.

MODEL	CAPACITY [BTU/H] REFRIGERANT		LIQUID LINE [IN]	SUCTION LINE [IN]	CONDENSING UNIT
AP26BCF-3T	102,000	404A	<sup>7</sup> / <sub>8</sub>	2 <sup>1</sup> / <sub>8</sub>	BLV220BM6CAP

**Note:** Refrigeration shall be a medium temp. system (40°F to -10°F SST), rated @ 14°F SST, 105°F Cond.

#### **OPTIONS:**

**Cabinet Sterilization:** The ultraviolet system sterilizes all metal surfaces within the cabinet in a preset time of 30 minutes.

**USB HACCP Interface:** Use a standard USB thumb drive to easily download HACCP data. The information recorded includes date, time, cycle identification, recipe name, and product core temperature at prescribed intervals.

**Wi-Fi Connectivity:** Supported functions include peer-topeer connectivity, remote monitoring over the local network, HACCP data download and alarm notifications via e-mail.

**2" or 4" Insulated Floor Panels:** Allow for height increase to detail shown above.

## **Remote Refrigeration**

## **Prison Security Package**

**Extra Food Probes:** One probe is standard, up to three additional food probes can be provided.

**Mobile Racks:** Model AP26BCF-3T can accommodate three mobile racks with maximum dimensions of 26" wide, 36" deep and 73 <sup>1</sup>/<sub>2</sub>" high.

**Reversed Cabinet:** The entire assembly is manufactured so that it is a mirror image of the cabinet shown above.

**Second Door:** For pass-thru operation (increases depth by 2")

**INSTALLATION:** A detailed installation manual is provided. It must be carefully followed to ensure proper operation and to protect your rights under the warranty.

**WARRANTY:** The warranty covers all parts found to be defective and the labor required to replace them for a period of one year from the date of shipment. Warranty excludes food probes.